

Knapstein

ZERA-3

Oberfläche

- níquel
- negro
- bronce

Version

- Cubierta del prisma
- Cubierta acrílica

Technical details

País de la Fabricación

fabricante

año

material

ajuste de altura

Atenuación

Potencia en vatios

LED#

Indice de reproduccion cromatica

El flujo luminoso en Im

Temperatura de color en grados

Kelvin

protección

Volumen de suministro

entrada de tensión

dosel

reemplazo de la bombilla:

Dimensions

Alemania

Knapstein

2024

Acryl, Metall

altura ajustable

control por movimientos

6x12 W

inclusive

>90 7644

2.200-3.000

IP20

LED

230 - 240 Volt

120 x 5,5 x 5,5 cm

en el fabricante / en la

fabrica L 120 cm

Descripción

The Knapstein ZERA-3 is characterised by its exceptional functionality. The LED pendant lamp emits its light upwards and downwards at the same time. The uplight and downlight of the three lamp bodies can be switched and dimmed separately using gesture control (Knapstein Dynamic White). The light colour can be adjusted separately for the uplight and downlight to a warmer tone (from a colour temperature of 3,000 Kelvin warm white to 2,200 Kelvin extra warm white). All dimming and light colour settings are saved using the memory function and automatically reset the next time the light is switched on. The Knapstein ZERA-3 has a synchronisation function (master/follower light control) for adjusting the light intensity and light colour of all light sources on one side of the luminaire. Once the lamps have been set via the master reflector, the follower reflectors can also be set individually and independently of the master setting using the separate gesture control. The Knapstein ZERA-3 is switched on or off with a swiping hand movement in the sensor area of one of the three lamp bodies. To change the light intensity, the hand is held longer in the sensor area. The desired light colour can then be set by holding the hand in the sensor area for a longer period again.

The ZERA-3 lamp covers are available in two versions.

A prism cover / clear is for almost loss-free and glare-free light output. The prism cover of the lamp is flush with the lamp body and does not illuminate from the sides.

With the acrylic cover version / in white, the cover extends slightly over the edge of the lamp / not flush with the visible side edge and illuminates as well. The light is slightly more diffuse / more even in its illumination.

With the built-in lift height adjustment, the luminaire height can be continuously adjusted from approx. 70 cm - 170 cm. Thanks to two lifts per lamp body, the individual lamp bodies can be precisely positioned in height -

K-Meral GmbH & Co. KG | Sachsenweg 9 | Hambare A റ്റ്റെ- Zepting സല്പ് West Halle 4eli គែកម្លាក់ខ្លាំ Hall: +49 (0) 2381 - 905 9350 | Fax: +49 (0) 2381 - 905 9350 | Fax: +49 (0) 258 අവട ത്രെയ്യുട്ടി പ്രവേശ (0) 258 എന്നു പ്രവേശ

	visible. This pendant lamp is available in different surfaces.
K-Meral GmbH & Co. KG Sachsenweg 9 Hambau / Öko-Zentrum NRW / Halle 4 59073 Hamm	