

Knapstein

ZERA-3

Oberfläche

- nickel
- noir
- hronze

Version

- Couverture du prisme
- Couverture acrylique

Technical details

Pays de fabrication

fabricant

année

matériel

réglage de la hauteur

atténuation

Puissance en Watt

LED#

Indice de rendu des couleurs

Flux lumineux en lm

La température de couleur en Kelvin

protection

Contenu de la livraison

aptitude de tension

baldaquin

 $remplacement \ des \ ampoules:$

Dimensions

Allemagne

Knapstein

2024

Acryl, Metall

réglable en hauteur

controle gestuel

6x12 W inclus

>90

7644

2.200-3.000

IP20

LED

230 - 240 Volt

120 x 5,5 x 5,5 cm

chez le fabricant / a l'usine

L 120 cm

Description

The Knapstein ZERA-3 is characterised by its exceptional functionality. The LED pendant lamp emits its light upwards and downwards at the same time. The uplight and downlight of the three lamp bodies can be switched and dimmed separately using gesture control (Knapstein Dynamic White). The light colour can be adjusted separately for the uplight and downlight to a warmer tone (from a colour temperature of 3,000 Kelvin warm white to 2,200 Kelvin extra warm white). All dimming and light colour settings are saved using the memory function and automatically reset the next time the light is switched on. The Knapstein ZERA-3 has a synchronisation function (master/follower light control) for adjusting the light intensity and light colour of all light sources on one side of the luminaire. Once the lamps have been set via the master reflector, the follower reflectors can also be set individually and independently of the master setting using the separate gesture control. The Knapstein ZERA-3 is switched on or off with a swiping hand movement in the sensor area of one of the three lamp bodies. To change the light intensity, the hand is held longer in the sensor area. The desired light colour can then be set by holding the hand in the sensor area for a longer period again.

The ZERA-3 lamp covers are available in two versions.

A prism cover / clear is for almost loss-free and glare-free light output. The prism cover of the lamp is flush with the lamp body and does not illuminate from the sides.

With the acrylic cover version / in white, the cover extends slightly over the edge of the lamp / not flush with the visible side edge and illuminates as well. The light is slightly more diffuse / more even in its illumination.

With the built-in lift height adjustment, the luminaire height can be continuously adjusted from approx. 70 cm - 170 cm. Thanks to two lifts per lamp body, the individual lamp bodies can be precisely positioned in height -

K-Meral GmbH & Co. KG | Sachsenweg 9 | Hambareh റ്റ് പ്രവാദ്ധ പ്രവാദ്യ പ്ര

| | visible. This pendant lamp is available in different surfaces. |
|--|--|
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| | |
| K-Meral GmbH & Co. KG Sachsenweg 9 Hambau / Öko-Zentrum NRW / Halle 4 59073 Hamm | |